



**V I S T E K**  
I N C O R P O R A T E D

## SERIES 3200 VIBRATION ISOLATION PLATFORM SELECTION FOR LEICA MICROSCOPES

PART NUMBER	LEICA MICROSCOPE MODEL NUMBER
VIP3200-L-001	DML Series Compound
VIP3200-L-002A	DM IRB/M ASTP
VIP3200-L-002B	AS TP Micromanipulation System
VIP3200-L-003	DM RB/RM
VIP3200-L-004	AS LMD
VIP3200-L-005	MZ Series HL Base: M2FL3, M216, M212.5
VIP3200-L-006	MZ BF/DF Base
VIP3200-L-007	DM IL/IM
VIP3200-L-008	DM 4000 & 4500
VIP3200-L-009	DM INM 300 DUV
VIP3200-L-010	DM LS
VIP3200-L-011	Leica MEF4
VIP3200-L-012	Reichert MEF3
VIP3200-L-013	DM IRE2
VIP3200-L-014	DM 5000 & 6000
VIP3200-L-015	Leitz Laborlux 12
VIP3200-L-016	DMI 6000
VIP3200-L-017	AM6000 (DMI6000 + Eppendorf manip.)
VIP3200-L-018	DM 1000
VIP3200-L-019	DM2000, 2500, 3000
VIP3200-L-020	INM100 & INM100 IR
VIP3200-L-021	DMLM Material Control Scope
VIP3200-L-022	INM300 DUV
VIP3200-L-023	INM200 UV
VIP3200-L-024	LMD6000 (Scope & Dissection Sys
VIP3200-L-025	MZ16 w/ TL RCI Base
VIP3200-L-026A	Transmitted Light Base, TL ST & TL RC w/ St. Stage
VIP3200-L-026B	Transmitted Light Base, TL BFDF
VIP3200-L-026C	Transmitted Light Base, TL w/ IsoPro Stage, & TL RCI w/ either stage
VIP3200-L-026D	Leica M205FA
VIP3200-L-027	LSI System

October 2008

*Please check our web site – [www.vistekinc.com](http://www.vistekinc.com) – for the most up-to-date information.*